

Garant

Steel boring bar A.. SV95CL 95°, for indexable inserts VC.., left-hand, Shank Ø / insert size: 10/07mm


Order data

Order number	261355 10/07
GTIN	4045197948083
Item class	21T

Technical description

Pack of insert screws	269028 27
Clamping height L_2	9 mm
Centre offset L_3	7 mm
Minimum pre-drill $\varnothing D_{\min}$	12.5 mm
Insert size	7 mm
Overall length L	100 mm
suitable indexable insert	VC.. 0702..
Head length L_1	22 mm
ISO code toolholder	A10H SV95CR/L07
Neck width L_4	6.8 mm
Setting angle κ	95 degrees
Usable depth T	5 mm
Shank $\varnothing D_s$	10 mm
Standard	Works standard
Application type	left-hand
Boring depth up to	3×D

Through-coolant	yes
Application	External longitudinal turning
Type of product	Boring Bar

Accessories

Torque screwdriver with scale, to take interchangeable blades maximum torque 200 cNm	659957 200
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX6	674248 TX6