

Garant**Indexable insert for turning WNMA 080408, for medium machining, Type: HB7210-1****Order data**

Order number	252076 HB7210-1
GTIN	4062406059170
Item class	21G

Technical description

Feed f	0.3 - 0.7 mm/rev.
Corner radius	0.8 mm
Cutting depth a_p	0.4 - 6.5 mm
Main application	K
Tool material	Carbide
Cutting conditions	slightly interrupted
Grade	HB7210-1
Cutting speed v_c main application	100 - 450 m/min
Finishing/roughing assignment	Skrubbearbejdning-sletbearbejdning
Coating	TiCN
ISO code indexable insert	WNMA 080408

Number of changes/inserts	6
Tolerance	M
Type of product	Indexable insert for turning