

**Garant**
**Clamping toolholder SVLCL 107,5°, for indexable inserts VC., left-hand,  
Shank size / insert size: 10/07mm**

**Order data**

Order number	261307 10/07
GTIN	4045197948359
Item class	21T

**Technical description**

Functional width $L_4$	12 mm
Insert size	7 mm
Head length $L_1$	15 mm
Overall length $L$	70 mm
suitable indexable insert	VC.. 0702..
ISO code toolholder	SVLCR/L 1010E07
Pack of insert screws	269028 27
Shank size	10 mm
Standard	Works standard
Application type	left-hand
Through-coolant	no
Setting angle $\kappa$	107.5 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

---

## Accessories

Torque screwdriver with scale, to take interchangeable blades maximum torque 200 cNm

659957 200

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX6

674248 TX6