

Garant
**Clamping toolholder SVLCR 107,5°, for indexable inserts VC., right-hand,
Shank size / insert size: 10/07mm**

Order data

Order number	261306 10/07
GTIN	4045197948328
Item class	21T

Technical description

Overall length L	70 mm
Insert size	7 mm
Functional width L ₄	12 mm
Head length L ₁	15 mm
ISO code toolholder	SVLCR/L 1010E07
Pack of insert screws	269028 27
Shank size	10 mm
suitable indexable insert	VC.. 0702..
Standard	Works standard
Application type	right-hand
Through-coolant	no
Setting angle κ	107.5 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Torque screwdriver with scale, to take interchangeable blades maximum torque 200 cNm

659957 200

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX6

674248 TX6