

Garant
Clamping toolholder SRDCN 30°, for indexable inserts RC.X, neutral, Shank / insert size: 16/08mm

Order data

Order number	260611 16/08
GTIN	4062406059354
Item class	21T

Technical description

Overhang L ₁ neutral holders	16.4 mm
suitable indexable insert	RC.T 0803
ISO code toolholder	SRDCN 1616H08
Insert size	8 mm
Functional width L ₄ neutral holders	12 mm
Overall length L neutral holders	100 mm
Pack of insert screws	269028 29
Shank size	16 mm
Standard	Works standard
Application type	neutral
Through-coolant	no
Setting angle κ	30 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

