

Garant

**Clamping toolholder SVLCL 107,5°, for indexable inserts VC., left-hand,
Shank size / insert size: 8/07mm**



Order data

Order number	261307 8/07
GTIN	4045197948342
Item class	21T

Technical description

Head length L_1	15 mm
Overall length L	60 mm
Shank size	8 mm
Pack of insert screws	269028 27
Insert size	7 mm
Functional width L_4	10 mm
suitable indexable insert	VC.. 0702..
ISO code toolholder	SVLCR/L 0808D07
Standard	Works standard
Application type	left-hand
Through-coolant	no
Setting angle κ	107.5 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Torque screwdriver with scale, to take interchangeable blades maximum torque 200 cNm

659957 200

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX6

674248 TX6