

**Garant****Clamping toolholder SVLCL 107,5°, for indexable inserts VC., left-hand,  
Shank size / insert size: 12/07mm****Order data**

Order number	261307 12/07
GTIN	4045197948366
Item class	21T

**Technical description**

Head length L <sub>1</sub>	18 mm
ISO code toolholder	SVLCR/L 1212F07
Insert size	7 mm
Shank size	12 mm
Overall length L	80 mm
suitable indexable insert	VC.. 0702..
Pack of insert screws	269028 27
Functional width L <sub>4</sub>	16 mm
Standard	Works standard
Application type	left-hand
Through-coolant	no
Setting angle κ	107.5 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

---

## Accessories

Torque screwdriver with scale, to take interchangeable blades maximum torque 200 cNm

659957 200

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX6

674248 TX6