

**Garant**
**Clamping toolholder SRGCR 30°, for indexable inserts RC.X, right-hand,  
Shank / insert size: 20/06mm**

**Order data**

Order number	260606 20/06
GTIN	4062406059408
Item class	21T

**Technical description**

Overall length L	125 mm
Head length L <sub>1</sub>	15.3 mm
suitable indexable insert	RC.T 0602
Shank size	20 mm
Functional width L <sub>4</sub>	25 mm
Insert size	6 mm
Pack of insert screws	269028 22
ISO code toolholder	SRGCR/L 2020K06
Standard	Works standard
Application type	right-hand
Through-coolant	no
Setting angle $\kappa$	30 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

---

## Accessories

Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm

659957 500

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8

674248 TX8