

**Garant**

**Clamping toolholder SRGCL 30°, for indexable inserts RC.X, left-hand, Shank / insert size: 12/06mm**


**Order data**

|              |               |
|--------------|---------------|
| Order number | 260607 12/06  |
| GTIN         | 4062406059453 |
| Item class   | 21T           |

**Technical description**

|                                 |                               |
|---------------------------------|-------------------------------|
| Shank size                      | 12 mm                         |
| Pack of insert screws           | 269028 22                     |
| Insert size                     | 6 mm                          |
| Overall length L                | 80 mm                         |
| Functional width L <sub>4</sub> | 16 mm                         |
| Head length L <sub>1</sub>      | 13.6 mm                       |
| ISO code toolholder             | SRGCR/L 1212F06               |
| suitable indexable insert       | RC.T 0602                     |
| Standard                        | Works standard                |
| Application type                | left-hand                     |
| Through-coolant                 | no                            |
| Setting angle $\kappa$          | 30 degrees                    |
| Application                     | External longitudinal turning |
| Application                     | External longitudinal turning |
| Type of product                 | Boring bar                    |

---

## Accessories

Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm

659957 500

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8

674248 TX8