

**Garant**

**Clamping toolholder SVVCN 72,5°, for indexable inserts VC., neutral, Shank / insert size: 12/07mm**



## Order data

Order number	261317 12/07
GTIN	4045197948373
Item class	21T

## Technical description

suitable indexable insert	VC.. 0702..
Pack of insert screws	269028 27
ISO code toolholder	SVVCN 1212M07
Overhang L <sub>1</sub> neutral holders	18 mm
Functional width L <sub>4</sub> neutral holders	6 mm
Overall length L neutral holders	150 mm
Shank size	12 mm
Insert size	7 mm
Standard	Works standard
Application type	neutral
Through-coolant	no
Setting angle κ	72.5 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Application	External longitudinal turning

Type of product

Boring bar

---

**Accessories**

Torque screwdriver with scale, to take interchangeable blades maximum torque 200 cNm

659957 200

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX6

674248 TX6