

Garant

Clamping toolholder SVVCN 72,5°, for indexable inserts VC., neutral, Shank / insert size: 8/07mm



Order data

Order number	261317 8/07
GTIN	4045197948403
Item class	21T

Technical description

suitable indexable insert	VC.. 0702..
Insert size	7 mm
Pack of insert screws	269028 27
Shank size	8 mm
Overall length L neutral holders	125 mm
ISO code toolholder	SVVCN 0808K07
Functional width L ₄ neutral holders	4 mm
Overhang L ₁ neutral holders	15 mm
Standard	Works standard
Application type	neutral
Through-coolant	no
Setting angle κ	72.5 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Application	External longitudinal turning

Type of product

Boring bar

Accessories

Torque screwdriver with scale, to take interchangeable blades maximum torque 200 cNm

659957 200

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX6

674248 TX6