

Garant

Clamping toolholder SRGCL 30°, for indexable inserts RC.X, left-hand, Shank / insert size: 25/06mm



Order data

| | |
|--------------|---------------|
| Order number | 260607 25/06 |
| GTIN | 4062406059484 |
| Item class | 21T |

Technical description

| | |
|---------------------------------|-------------------------------|
| suitable indexable insert | RC.T 0602 |
| Functional width L ₄ | 32 mm |
| Head length L ₁ | 15.3 mm |
| Overall length L | 150 mm |
| Pack of insert screws | 269028 22 |
| ISO code toolholder | SRGCR/L 2525M06 |
| Insert size | 6 mm |
| Shank size | 25 mm |
| Standard | Works standard |
| Application type | left-hand |
| Through-coolant | no |
| Setting angle κ | 30 degrees |
| Application | External longitudinal turning |
| Application | External longitudinal turning |
| Type of product | Boring bar |

Accessories

Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm

659957 500

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8

674248 TX8