

Garant**DNMG 150408, Type: HB7035-1****Order data**

Order number	250768 HB7035-1
GTIN	4045197949134
Item class	21G

Description

DNMG 150408 HB7035-1 Grade: HB7035-1

Chip breaker: SM

Tolerance: M

Cutting depth a_p : 0.5 - 5 mmFeed f : 0.2 - 0.5 mm/rev.Cutting speed v_c main application: 100 - 320 m/min**Technical description**

Feed f	0.2 - 0.5 mm/rev.
Cutting depth a_p	0.5 - 5 mm
Cutting speed v_c main application	100 - 320 m/min
Tool material	Carbide
Finishing/roughing assignment	Skrubbearbejdning-sletbearbejdning
Cutting conditions	heavily interrupted
Chip breaker	SM

Grade	HB7035-1
Main application	P
Corner radius	0.8 mm
ISO code indexable insert	DNMG 150408
Number of changes/inserts	4
Tolerance	M
Type of product	Indexable insert for turning