

Garant**DNMG 150412, Type: HB7010-1****Order data**

Order number	250769 HB7010-1
GTIN	4045197949141
Item class	21G

Description

DNMG 150412 HB7010-1 Grade: HB7010-1

Chip breaker: SM

Tolerance: M

Cutting depth a_p : 0.5 - 5 mmFeed f : 0.2 - 0.5 mm/rev.Cutting speed v_c main application: 120 - 440 m/min**Technical description**

Main application	P
Feed f	0.2 - 0.5 mm/rev.
Corner radius	1.2 mm
Cutting conditions	continuous
Grade	HB7010-1
Finishing/roughing assignment	Skrubbearbejdning-sletbearbejdning
Tool material	Carbide

Cutting speed v_c main application	120 - 440 m/min
Chip breaker	SM
Cutting depth a_p	0.5 - 5 mm
ISO code indexable insert	DNMG 150412
Number of changes/inserts	4
Tolerance	M
Type of product	Indexable insert for turning