

**Garant**

**Carbide boring bar E.. SDQCR 107,5°, for indexable inserts DC., right-hand,  
Shank Ø / insert size: 25/11mm**


**Order data**

Order number	260320 25/11
GTIN	4062406066062
Item class	21T

**Technical description**

Insert size	11 mm
ISO code toolholder	E25S SDQCR/L11
Minimum pre-drill Ø $D_{min}$	32 mm
Overhang $L_1$	65 mm
Setting angle $\kappa$	107.5 degrees
Centre offset $L_3$	16 mm
Pack of insert screws	269028 8
Overall length L	250 mm
suitable indexable insert	DC.. 11T3..
Clamping height $L_2$	24 mm
Shank Ø $D_s$	25 mm
Standard	DIN 8024
Application type	right-hand
Boring depth up to	8xD
Tool material	Carbide
Through-coolant	yes

Application	Internal longitudinal turning
Type of product	Boring Bar

---

## Accessories

Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15