

Garant**DNMG 150412, Type: HB7010-1****Order data**

Order number	250869 HB7010-1
GTIN	4045197949202
Item class	21G

Description

DNMG 150412 HB7010-1 Grade: HB7010-1

Chip breaker: SG

Cutting depth a_p : 1.5 - 6 mmFeed f : 0.25 - 0.6 mm/rev.Cutting speed v_c main application: 100 - 375 m/min**Technical description**

Cutting speed v_c main application	100 - 375 m/min
Cutting depth a_p	1.5 - 6 mm
Main application	P
Feed f	0.25 - 0.6 mm/rev.
Cutting conditions	continuous
Tool material	Carbide
Chip breaker	SG

Grade	HB7010-1
Finishing/roughing assignment	Roughing
Corner radius	1.2 mm
ISO code indexable insert	DNMG 150412
Number of changes/inserts	4
Type of product	Indexable insert for turning