

Garant**Burr Z FINE – very fine, Carbide, Type: M1020****Order data**

Order number	540440 M1020
GTIN	4045197966797
Item class	51D

Description**Version:**

Shank \varnothing 6 mm.

GARANT burrs are manufactured from high performance carbide grades with high wear resistance and maximum cutting edge strength, using only the latest CNC machines. Steel shanks are used when the head diameter is larger than the shank diameter, otherwise they are made from solid carbide. **Pointed cone shape** (SKM).

Application:

Suitable for use with power tools and industrial robots, on almost all materials. For deburring, edge breaking, cleaning, weld and surface preparation.

Technical description

Head \varnothing	10 mm
Shape description	pointed cone
Tooth type abbreviation	Z FINE
Shank \varnothing	6 mm
Overall length	60 mm
Shape	M1020
Toothing grit designation	very fine
Head length	20 mm
Series	Tooth configuration Z FINE
Tool material	Carbide

Type of product

Burr

User data

	Suitability	V_c	ISO code
Steel < 900 N/mm ²	suitable		
Steel < 1400 N/mm ²	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable		
INOX	suitable		
Ti	suitable		
GG(G)	suitable		