

Garant**Cutting disc, high-performance version EXTRA THIN, steel, Disc Ø: 125mm****Order data**

Order number	563262 125
GTIN	4045197967510
Item class	51M

Description**Version:**

New **high-performance version** using state of the art technology with significant productivity advantages and excellent cutting qualities. **Increased cutting performance** due to rough free-grinding side faces; **improved service life**.

The thinness of the disc allows **very quick** cutting **with low force and optimum time saving**.

Clean cut edges, virtually no burrs.

Special type for **steel**, high performance version.

Specification:

A60S-BF.

Technical description

maximum speed	12200 min ⁻¹
Specification	A60S-BF
Disc Ø	125 mm
Shape	41

Bore Ø	22.23 mm
Disc thickness	1 mm
Shape description	flat
for material thicknesses	3 mm
Grinding medium code	A
recommended approach angle	90 degrees
optimised for material	HSS
Propulsive equipment	Angle grinders
maximum circumferential speed	80 m/s
Type of product	Cutting disc

User data

	Suitability	V _c	ISO code
Steel < 900 N/mm ²	suitable		
Steel < 1400 N/mm ²	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable		
GG(G)	suitable only under restricted conditions		
Plastic, GRP	suitable only under restricted conditions		
dry	suitable		