



## Universal clamp (clamping hand), Type: 50



### Order data

Order number	861900 50
GTIN	4045197167521
Item class	82C

### Description

**Version:**

With trapezoidal thread spindle and 2 swing clamping jaws. Each clamping jaw has 3 smooth faces and a cross-Vee face; can be used for **clamping the most diverse components**.

**Application:**

For **internal** and **external clamping** of the most diverse workpiece shapes.

**Material:**

Spindle and clamping block of burnished steel.

### Technical description

Capacity in compression a	0 - 50 mm
maximum clamping force	2000 N
Clamping depth c	30 mm
Capacity in tension b	32 - 82 mm
Type of product	Clamp

