



Universal clamp (clamping hand), Type: 75



Order data

Order number	861900 75
GTIN	4045197167538
Item class	82C

Description

Version:

With trapezoidal thread spindle and 2 swing clamping jaws. Each clamping jaw has 3 smooth faces and a cross-Vee face; can be used for **clamping the most diverse components**.

Application:

For **internal** and **external clamping** of the most diverse workpiece shapes.

Material:

Spindle and clamping block of burnished steel.

Technical description

Clamping depth c	50 mm
Capacity in compression a	0 - 75 mm
maximum clamping force	2500 N
Capacity in tension b	40 - 115 mm
Type of product	Clamp

