

**Double ratchet ring spanner, Widths across flats: 19X22mm****Order data**

Order number	614843 19X22
GTIN	4045197973344
Item class	62A

Description**Version:**

Drop-forged. With close tolerance jaw widths. Reversible for left- and right-hand tightening, plus centre position. With unequal jaw widths, deep cranked. Extremely small working arc of 5°.

Material:

Chrome vanadium steel, matt chrome-plated.

Technical description

Width across flats 1	19 mm
maximum ring \varnothing D2	48 mm
Width across flats 2	22 mm
maximum ring \varnothing D1	35 mm
overall length L	300 mm
maximum ring height h_2	30 mm
Width across flats	metric
maximum ring height h_1	24 mm
No. of teeth	72
Working arc	5 degrees
Manufacturing process	drop forged
Material	Chrome vanadium steel

Surface	matt chrome-plated
Ring end cranked	yes
Ratchet reversible	no
Type of product	Spanner