

**Double ratchet ring spanner, Widths across flats: 24X27mm****Order data**

Order number	614843 24X27
GTIN	4045197973368
Item class	62A

**Description****Version:**

Drop-forged. With close tolerance jaw widths. Reversible for left- and right-hand tightening, plus centre position. With unequal jaw widths, deep cranked. Extremely small working arc of 5°.

**Material:**

Chrome vanadium steel, matt chrome-plated.

**Technical description**

Width across flats	metric
overall length L	330 mm
Width across flats 2	27 mm
maximum ring height $h_1$	30 mm
maximum ring $\varnothing$ D2	60 mm
maximum ring $\varnothing$ D1	48 mm
Width across flats 1	24 mm
maximum ring height $h_2$	34 mm
No. of teeth	72
Working arc	5 degrees
Manufacturing process	drop forged
Material	Chrome vanadium steel

Surface	matt chrome-plated
Ring end cranked	yes
Ratchet reversible	no
Type of product	Spanner