

Garant**Jobber drill HSS-E VA, uncoated, Ø DC h8: 14mm****Order data**

Order number	116360 14
GTIN	4045197031860
Item class	11C

Description**Version:****With strengthened core.**

Specially treated surface, reducing edge build up and improving chip evacuation.

With point geometry shape C.

Recommendation:**Maximum drilling depth:**

$$L_2 = L_c - 1.5 \times D_c.$$

Note:

For suitable reducing adapters for tools with MT shanks see **No. 343000-343530**.

Technical description

Feed f in steel < 750 N/mm ²	0.16 mm/rev.
Flute length L _c	108 mm
Number of cutting edges Z	2
Nominal Ø D _c	14 mm
Tolerance nominal Ø	h8
Overall length L	189 mm
Morse taper MT size	1
Standard	DIN 345
recommended maximum drilling depth L ₂	87 mm
Point angle	135 degrees

Shank	Morse taper
Coating	uncoated
Tool material	HSS E
Type	INOX
Helix angle	35-40 degrees
Through-coolant	no
Colour ring	without
Type of product	Jobber drill

User data

	Suitability	V _c	ISO code
Steel < 500 N/mm ²	suitable	40 m/min	P
Steel < 750 N/mm ²	suitable	30 m/min	P
Steel < 900 N/mm ²	suitable	25 m/min	P
Steel < 1100 N/mm ²	suitable	10 m/min	P
INOX < 900 N/mm ²	suitable	12 m/min	M
Ti > 850 N/mm ²	suitable	5 m/min	S
GG(G)	suitable	25 m/min	K
CuZn	suitable	80 m/min	N
Oil	suitable		
wet maximum	suitable		