


**Garant**

**Steel boring bar A.. SCLCL 95°, for indexable inserts CC., right-hand, Shank Ø / insert size: 0608/06mm**



## Order data

Order number	260032 0608/06
GTIN	4045197978790
Item class	21T

## Technical description

Setting angle $\kappa$	95 degrees
suitable indexable insert	CC.. 0602..
Neck width $L_4$	6 mm
Clamping height $L_2$	7 mm
Insert size	6 mm
Pack of insert screws	269028 7
Minimum pre-drill $\varnothing D_{\min}$	8 mm
Head length $L_1$	21.5 mm
Centre offset $L_3$	4.2 mm
Overall length $L$	100 mm
ISO code toolholder	A0608H SCLCR/L06
Shank $\varnothing D_s$	8 mm
Standard	Works standard
Application type	right-hand
Boring depth up to	3×D
Through-coolant	yes

Application	Internal longitudinal turning
Type of product	Boring Bar

---

## Accessories

Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8