

Garant
GARANT Master Tap machine tap HSS-E-PM Form C, ALTiX, M: M2,6

Order data

Order number	135960 M2,6
GTIN	4045197984296
Item class	11I

Description
Version:

Universal taps, designed for use in a wide spectrum of materials with high process reliability.

- **HSS-E-PM tool material for a high degree of wear resistance.**
- **Reduced coefficient of friction due to the new high-performance coating.**
- **Special geometry for optimum swarf evacuation.**

Corresponds to **ISO 2X/6HX**.

Thread type: M

Tool material: HSS E PM

Standard: DIN 371

Tolerance class: ISO 2X 6HX

Thread pitch: 0.45 mm

Overall length L: 50 mm

Shank $\varnothing D_s$: 2.8 mm

Shank square \square : 2.1 mm

Tapping hole \varnothing : 2.15 mm

Technical description

Tapping hole \varnothing	2.15 mm
Tool material	HSS E PM
Standard	DIN 371
Tolerance class	ISO 2X 6HX
Thread pitch	0.45 mm
Number of cutting edges Z	2

Shank $\varnothing D_s$	2.8 mm
Thread \varnothing	2.6 mm
Number of clamping slots	2
Thread depth	6.5 mm
Overall length L	50 mm
Shank square \square	2.1 mm
Thread type	M
Thread size	M2.6
Coating	AlTiX
Flank angle	60°
Thread standard	DIN 13
Taper lead form	C
Helix angle	40°
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 2.5×D for blind holes
Cutting direction	right-hand
Type of threading tool	Machine tap for dynamic machining
Colour ring	green
Series	Master Tap
Type of product	Tap

User data

	Suitability	V_c	ISO code
Alu plastics	suitable	30 m/min	N
Aluminium (short chipping)	Suitable	35 m/min	N
Alu > 10% Si	suitable	20 m/min	N
Steel < 500 N/mm ²	suitable	30 m/min	P

Steel < 750 N/mm ²	suitable	30 m/min	P
Steel < 900 N/mm ²	suitable	25 m/min	P
Steel < 1100 N/mm ²	suitable	12 m/min	P
Steel < 1400 N/mm ²	suitable	8 m/min	P
INOX < 900 N/mm ²	suitable	10 m/min	M
INOX > 900 N/mm ²	suitable	8 m/min	M
GG(G)	suitable	20 m/min	K
CuZn	suitable	20 m/min	N
Uni	suitable		
Oil	suitable		
wet maximum	suitable		