

Garant
Solid carbide end mill HPC, ZOX, Ø f8 DC: 5mm

Order data

Order number	202549 5
GTIN	4045197454249
Item class	11X

Description
Version:

Sturdy roughing slot drills **without** knuckle profile.

With strong core, **special chip breaker recesses** and **large polished flutes**.

Application:

For roughing milling with high demands on the component surface.

Technical description

No. of teeth Z	4
Recess Ø D ₁	4.7 mm
Feed f _z for slot milling in short-chipping aluminium	0.06 mm
Shank form	HA
Feed f _z for side milling in short-chipping aluminium	0.08 mm
Corner chamfer width at 45°	0.1 mm
Overhang length L ₁ incl. recess	24 mm
Cutting edge Ø D _c	5 mm
Shank Ø D _s	6 mm
Overall length L	62 mm
Flute length L _c	17 mm
Direction of infeed	horizontal, oblique and vertical
Shank	DIN 6535 HA to h6

Tolerance nominal Ø	f8
Balance quality with shank	G 2.5 with HA
Helix angle	45 degrees
Corner chamfer angle	45 degrees
Coating	ZOX
Tool material	Solid carbide
Standard	Manufacturer's standard
Type	W
Helix angle characteristic	unequal spacing
Spacing of the cutters	unequal spacing
Cutting width a_e for milling operation	0.3×D for side milling
Through-coolant	no
Machining strategy	HPC
Colour ring	yellow
Type of product	End / face mill

User data

	Suitability	V_c	ISO code
Aluminium	suitable only under restricted conditions	500 m/min	N
Aluminium (short chipping)	suitable	480 m/min	N
Alu > 10% Si	suitable	240 m/min	N
Hybrids	suitable only under restricted conditions	m/min	N
Honeycomb sandwich	suitable only under restricted conditions	m/min	N
CuZn	Suitable	240 m/min	N
wet maximum	suitable		
wet minimum	suitable		

dry	suitable only under restricted conditions
Air	suitable only under restricted conditions
Services	
Shank grinding Type HB	129100 HB