

Garant
Top jaw Gripp, single piece, for type: 100GS

Order data

Order number	361123 100GS
GTIN	4045197985934
Item class	310

Description
Version:

Clamping step with a height of 5 mm and 3 mm contact area.

Application:

Ideal for rough machining.

Suitable for:

5-axis vice set No. 361100 and clamping module No. 361105 – 361110.

Supplied with:

Fastening screws.

Note:

Type GS with gripp step and smooth clamping step

Technical description

Height h_1	5 mm
suitable for colour code	Xpent0
Jaw width b	100 mm
Length l_2	3 mm
Jaw height h	40 mm
Jaw length l	60 mm

Length l_1	3 mm
Height h_2	5 mm
Type of product	Vice jaws