

Garant**NC spotting drill HSS-E 90° N, uncoated, Ø DC h6: 10mm****Order data**

Order number	112000 10
GTIN	4045197001078
Item class	11A

Description**Version:**

≥ Ø 6 mm with **drive flat to DIN 1835-B.**

Precision centred ground point with thin chisel edge - gives easy spot drilling and high accuracy of the centre hole form. Very sturdy due to short flutes.

Note:

Use speed for the actual hole Ø
(not necessarily the speed for the drill outer Ø).

Shank: DIN 1835 B to h6

Flute length L_c : 25 mm

Overall length L: 89 mm

Shank Ø D_s : 10 mm

Feed f in steel < 900 N/mm²: 0.07 mm/rev.

Technical description

Feed f in steel < 900 N/mm ²	0.07 mm/rev.
Flute length L_c	25 mm
Nominal Ø D_c	10 mm
Shank tolerance	h6
Shank Ø D_s	10 mm
Overall length L	89 mm
Shank	DIN 1835 B to h6
Coating	uncoated

Tool material	HSS E
Standard	Manufacturer's standard
Type	N
Tolerance nominal Ø	h6
Point angle	90 °
Number of cutting edges Z	2
Through-coolant	no
Colour ring	without
Type of product	Spotting drill

User data

	Suitability	V _c	ISO code
Alu plastics	suitable	70 m/min	N
Aluminium (short chipping)	suitable	45 m/min	N
Steel < 500 N/mm ²	suitable	40 m/min	P
Steel < 750 N/mm ²	suitable	30 m/min	P
Steel < 900 N/mm ²	suitable	25 m/min	P
Steel < 1100 N/mm ²	suitable	10 m/min	P
Steel < 1400 N/mm ²	suitable	8 m/min	P
INOX < 900 N/mm ²	suitable	12 m/min	M
INOX > 900 N/mm ²	suitable	8 m/min	M
CuZn	suitable	80 m/min	N
Uni	suitable		
Oil	suitable		
wet maximum	suitable		