

Garant

GARANT Master Steel PickPocket solid carbide roughing end mill HPC, TiAlN, Ø f8 DC: 12mm



Order data

Order number	202406 12
GTIN	4045197781451
Item class	11X

Description

Version:

For **roughing and finishing**

With corner radii similar to torus cutters.

Up to 1xD into solid material **at very high feed rates** with smooth cutting action.

Advantage:

Optimised flute form, eccentric relief ground, wide chip space.

Technical description

Overhang length L_1 incl. recess	46 mm
Shank Ø D_s	12 mm
Direction of infeed	horizontal, oblique and vertical
Feed f_z for side milling in steel < 900 N/mm ²	0.09 mm
No. of teeth Z	3
Tolerance nominal Ø	f8
Flute length L_c	26 mm
Cutting edge Ø D_c	12 mm
Recess Ø D_1	11.6 mm
Shank	DIN 6535 HB to h6
Overall length L	93 mm

Feed f_z for slot milling in steel < 900 N/mm ²	0.07 mm
Helix angle	38 degrees
Corner rounding r_v	0.6 mm
Series	Master Steel
Coating	TiAlN
Tool material	Solid carbide
Standard	Manufacturer's standard
Type	N
Helix angle characteristic	unequal spacing
Spacing of the cutters	unequal spacing
Cutting width a_e for milling operation	0.4×D for side milling
Cutting width a_e for milling operation	Full slot cutting depth 1×D
Through-coolant	no
Machining strategy	HPC
Colour ring	green
Type of product	End / face mill

User data

	Suitability	V_c	ISO code
Steel < 500 N/mm ²	suitable	260 m/min	P
Steel < 750 N/mm ²	suitable	240 m/min	P
Steel < 900 N/mm ²	suitable	190 m/min	P
Steel < 1100 N/mm ²	suitable	180 m/min	P
Steel < 1400 N/mm ²	suitable only under restricted conditions	150 m/min	P
INOX < 900 N/mm ²	suitable	80 m/min	M
INOX > 900 N/mm ²	suitable	70 m/min	M
GG(G)	suitable	250 m/min	K
Uni	suitable		

wet maximum	suitable
wet minimum	suitable only under restricted conditions
dry	suitable
Air	suitable