

Garant

**Clamping toolholder SRGCR 30°, for indexable inserts RC.X, right-hand,
Shank / insert size: 12/06mm**



Order data

Order number	260606 12/06
GTIN	4062406059385
Item class	21T

Technical description

ISO code toolholder	SRGCR/L 1212F06
Head length L ₁	13.6 mm
Overall length L	80 mm
Insert size	6 mm
Shank size	12 mm
suitable indexable insert	RC.T 0602
Functional width L ₄	16 mm
Pack of insert screws	269028 22
Standard	Works standard
Application type	right-hand
Through-coolant	no
Setting angle κ	30 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm

659957 500

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8

674248 TX8