

**Garant**
**Clamping toolholder SRGCR 30°, for indexable inserts RC.X, right-hand,  
Shank / insert size: 25/08mm**

**Order data**

Order number	260606 25/08
GTIN	4062406059446
Item class	21T

**Technical description**

Pack of insert screws	269028 29
Overall length L	150 mm
ISO code toolholder	SRGCR/L 2525M08
Insert size	8 mm
Head length L <sub>1</sub>	19.8 mm
Shank size	25 mm
Functional width L <sub>4</sub>	32 mm
suitable indexable insert	RC.T 0803
Standard	Works standard
Application type	right-hand
Through-coolant	no
Setting angle κ	30 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

