

Garant
Clamping toolholder SRGCL 30°, for indexable inserts RC.X, left-hand, Shank / insert size: 16/06mm

Order data

Order number	260607 16/06
GTIN	4062406059460
Item class	21T

Technical description

Pack of insert screws	269028 22
ISO code toolholder	SRGCR/L 1616H06
Head length L ₁	13.6 mm
suitable indexable insert	RC.T 0602
Overall length L	100 mm
Shank size	16 mm
Insert size	6 mm
Functional width L ₄	20 mm
Standard	Works standard
Application type	left-hand
Through-coolant	no
Setting angle κ	30 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm

659957 500

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8

674248 TX8