

Garant

**Clamping toolholder SRGCR 30°, for indexable inserts RC.X, right-hand,
Shank / insert size: 16/08mm**



Order data

Order number	260606 16/08
GTIN	4062406059422
Item class	21T

Technical description

Functional width L ₄	20 mm
Head length L ₁	18.8 mm
ISO code toolholder	SRGCR/L 1616H08
Insert size	8 mm
suitable indexable insert	RC.T 0803
Pack of insert screws	269028 29
Overall length L	100 mm
Shank size	16 mm
Standard	Works standard
Application type	right-hand
Through-coolant	no
Setting angle κ	30 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

