

Garant
**Clamping toolholder SRGCR 30°, for indexable inserts RC.X, right-hand,
Shank / insert size: 20/08mm**

Order data

Order number	260606 20/08
GTIN	4062406059439
Item class	21T

Technical description

Head length L_1	14.7 mm
Functional width L_4	25 mm
Pack of insert screws	269028 29
Shank size	20 mm
ISO code toolholder	SRGCR/L 2020K08
Overall length L	125 mm
Insert size	8 mm
suitable indexable insert	RC.T 0803
Standard	Works standard
Application type	right-hand
Through-coolant	no
Setting angle κ	30 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

