

**Garant****Clamping toolholder SRGCL 30°, for indexable inserts RC.X, left-hand, Shank / insert size: 20/08mm****Order data**

Order number	260607 20/08
GTIN	4062406059507
Item class	21T

**Technical description**

ISO code toolholder	SRGCR/L 2020K08
Head length L <sub>1</sub>	14.7 mm
Pack of insert screws	269028 29
Overall length L	125 mm
suitable indexable insert	RC.T 0803
Insert size	8 mm
Shank size	20 mm
Functional width L <sub>4</sub>	25 mm
Standard	Works standard
Application type	left-hand
Through-coolant	no
Setting angle $\kappa$	30 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

