

**Garant**
**Clamping toolholder SRGCL 30°, for indexable inserts RC.X, left-hand, Shank / insert size: 16/08mm**

**Order data**

Order number	260607 16/08
GTIN	4062406059491
Item class	21T

**Technical description**

Functional width $L_4$	20 mm
Shank size	16 mm
ISO code toolholder	SRGCR/L 1616H08
Head length $L_1$	18.8 mm
Overall length $L$	100 mm
Pack of insert screws	269028 29
suitable indexable insert	RC.T 0803
Insert size	8 mm
Standard	Works standard
Application type	left-hand
Through-coolant	no
Setting angle $\kappa$	30 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

