

Garant

Clamping toolholder SRGCL 30°, for indexable inserts RC.X, left-hand, Shank / insert size: 20/06mm


Order data

Order number	260607 20/06
GTIN	4062406059477
Item class	21T

Technical description

Shank size	20 mm
Insert size	6 mm
Overall length L	125 mm
ISO code toolholder	SRGCR/L 2020K06
Functional width L ₄	25 mm
Head length L ₁	15.3 mm
Pack of insert screws	269028 22
suitable indexable insert	RC.T 0602
Standard	Works standard
Application type	left-hand
Through-coolant	no
Setting angle κ	30 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm

659957 500

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8

674248 TX8