

**Garant**

**Clamping toolholder SRGCL 30°, for indexable inserts RC.X, left-hand, Shank / insert size: 25/08mm**



## Order data

Order number	260607 25/08
GTIN	4062406059514
Item class	21T

## Technical description

Overall length L	150 mm
ISO code toolholder	SRGCR/L 2525M08
Pack of insert screws	269028 29
suitable indexable insert	RC.T 0803
Head length L <sub>1</sub>	19.8 mm
Shank size	25 mm
Functional width L <sub>4</sub>	32 mm
Insert size	8 mm
Standard	Works standard
Application type	left-hand
Through-coolant	no
Setting angle κ	30 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

