

Garant
Jobber drill, extra long HSS-E N, TiAlN, Ø DC h8 × overall length L: 10X430mm

Order data

Order number	116285 10X430
GTIN	4045197328052
Item class	11B

Description
Version:

TiAlN and anti-friction coating, low wear and low tendency to edge build-up.
With point geometry shape C.

Advantage:

Flute length to DIN 340. For high-tensile tempered steels, **including TOOLOX.**

Recommendation:
Maximum drilling depth:

$$L_2 = L_c - 1.5 \times D_c.$$

Note:

Suitable NC spotting drills No. 112103, 112110 and 112160 with **120° tip angle** for enhanced process reliability

Technical description

Feed f in steel < 750 N/mm ²	0.1 mm/rev.
Number of cutting edges Z	2
Nominal Ø D _c	10 mm
Flute length L _c	121 mm
Tolerance nominal Ø	h8
Shank Ø D _s	10 mm
Overall length L	430 mm
Standard	DIN 1869
recommended maximum drilling depth L ₂	106 mm

Point angle	118 degrees
Shank	Plain shank
Coating	TiAlN
Tool material	HSS E
Type	N
Helix angle	38 degrees
Through-coolant	no
Colour ring	red
Type of product	Jobber drill

User data

	Suitability	V _c	ISO code
Steel < 500 N/mm ²	suitable only under restricted conditions	38 m/min	P
Steel < 750 N/mm ²	suitable	28 m/min	P
Steel < 900 N/mm ²	suitable	22 m/min	P
Steel < 1100 N/mm ²	suitable	7 m/min	P
Steel < 1400 N/mm ²	suitable	5 m/min	P
TOOLOX 33	suitable	10 m/min	H
TOOLOX 44	suitable	8 m/min	H
INOX < 900 N/mm ²	suitable only under restricted conditions	10 m/min	M
INOX > 900 N/mm ²	suitable only under restricted conditions	5 m/min	M
CuZn	suitable only under restricted conditions	70 m/min	N
Oil	suitable		
wet maximum	suitable		