

Garant
Solid carbide milling cutter, Diamond, Ø f8 DC: 10mm

Order data

Order number	209713 10
GTIN	4045197512529
Item class	10Y

Description
Version:

With the latest generation of **crystalline diamond coating sp³**, for process reliability in machining **fibre-reinforced composites, CRP, GRP, and graphite.**

Dynamic cutter geometry.
Technical description

Feed f_z for slot milling in GRP CRP	0.06 mm
Cutting edge $\varnothing D_c$	10 mm
Corner chamfer width at 45°	0.2 mm
Recess $\varnothing D_1$	9.7 mm
Overhang length L_1 incl. recess	30 mm
No. of teeth Z	4
Feed f_z for slot milling in graphite	0.06 mm
Shank $\varnothing D_s$	10 mm
Overall length L	72 mm
Flute length L_c	22 mm
Direction of infeed	horizontal, oblique and vertical
Shank	DIN 6535 HA with h6
Tolerance nominal \varnothing	f8

Balance quality with shank	G 2.5 with HA
Helix angle	45 degrees
Corner chamfer angle	45 degrees
Coating	Diamond
Tool material	Solid carbide
Standard	Manufacturer's standard
Spacing of the cutters	unequal spacing
Cutting width a_e for milling operation	Full slot cutting depth $1 \times D$
Through-coolant	no
Colour ring	black
Type of product	End / face mill

User data

	Suitability	V_c	ISO code
PVDF GF20	suitable	200 m/min	N
POM GF25	suitable	190 m/min	N
PA 66 GF30	suitable	170 m/min	N
PEEK GF30	suitable	150 m/min	N
PTFE CF25	suitable	180 m/min	N
PEEK CF30	suitable	160 m/min	N
Hybrids	suitable		
Honeycomb sandwich	suitable	350 m/min	N
GRP	suitable	190 m/min	N
GRP, CRP	suitable	190 m/min	N
Graphite	suitable	340 m/min	N
wet minimum	suitable		
dry	Suitable		
Air	suitable		

Services

Shank grinding Type HB

129100 HB