

Version	Revision Date:	SDS Number:	Date of last issue: -
1.0	08.11.2018	330000000017	Date of first issue: 16.11.2016

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1 Product identifier

Trade name : GARANT diamond paste 5g

1.2 Relevant identified uses of the substance or mixture and uses advised against

Use of the Sub- : Abrasive, Lapping agent
stance/Mixture

FOR THIS PRODUCT, IT IS NOT REQUIRED A SAFETY DATA SHEET ACCORDING TO THE EU LEGISLATION

1.3 Details of the supplier of the safety data sheet

Company : Hoffmann Nürnberg GmbH Qualitätswerkzeuge
Franz-Hoffmann-Straße 3
DE-90431 Nürnberg
Phone : +49 (0) 911 6581-0
Fax : +49 (0) 911 6581-317
Email address of the : dangerousgoods@hoffmann-group.com
responsible person

1.4 Emergency telephone number

Hoffmann Nürnberg GmbH Phone: +49 (0) 911 6581-0 (business hours from 8:00 - 15.00 o'clock)
Email: dangerousgoods@hoffmann-group.com

SECTION 2: Hazards identification

2.1 Classification of the substance or mixture

Classification (REGULATION (EC) No 1272/2008)
Not a hazardous substance or mixture.

2.2 Label elements

Labelling (REGULATION (EC) No 1272/2008)
Not a hazardous substance or mixture.

2.3 Other hazards

This substance/mixture contains no components considered to be either persistent, bioaccumulative and toxic (PBT), or very persistent and very bioaccumulative (vPvB) at levels of 0.1% or higher.

SECTION 3: Composition/information on ingredients

Version	Revision Date:	SDS Number:	Date of last issue: -
1.0	08.11.2018	330000000017	Date of first issue: 16.11.2016

3.2 Mixtures

Hazardous components

Remarks : No hazardous ingredients

SECTION 4: First aid measures

4.1 Description of first aid measures

General advice : First Aid responders should pay attention to self-protection and use the recommended protective clothing
If symptoms persist, call a physician.

If inhaled : Move to fresh air in case of accidental inhalation of dust or fumes from overheating or combustion.

In case of skin contact : Take off contaminated clothing and shoes immediately.
Wash off with soap and plenty of water.

In case of eye contact : Protect unharmed eye.
Flush eyes with water as a precaution.
Remove contact lenses.
Keep eye wide open while rinsing.

If swallowed : Rinse mouth with water.
Drink 1 or 2 glasses of water.
Never give anything by mouth to an unconscious person.
Do NOT induce vomiting.
If symptoms persist, call a physician.

4.2 Most important symptoms and effects, both acute and delayed

Symptoms : Nausea
Discomfort
Dizziness
Vomiting

Risks : There are at present no indications to acute dangers for the health.

4.3 Indication of any immediate medical attention and special treatment needed

Treatment : Treat symptomatically.

SECTION 5: Firefighting measures

5.1 Extinguishing media

Suitable extinguishing media : In case of fire, use water/water spray/water jet/carbon dioxide/sand/foam/alcohol resistant foam/chemical powder for extinction.

Version	Revision Date:	SDS Number:	Date of last issue: -
1.0	08.11.2018	330000000017	Date of first issue: 16.11.2016

Unsuitable extinguishing media : High volume water jet

5.2 Special hazards arising from the substance or mixture

Specific hazards during fire- : May form explosive mixtures in air. fighting

Hazardous combustion products : See section 10.

5.3 Advice for firefighters

Special protective equipment for firefighters : Wear full protective clothing and self-contained breathing apparatus.

Further information : Standard procedure for chemical fires.

Collect contaminated fire extinguishing water separately. This must not be discharged into drains.

Fire residues and contaminated fire extinguishing water must be disposed of in accordance with local regulations.

SECTION 6: Accidental release measures

6.1 Personal precautions, protective equipment and emergency procedures

Personal precautions : Ensure adequate ventilation.
Use non-slip safety shoes in areas where spills or leaks can occur.
Material can create slippery conditions.
Evacuate personnel to safe areas.
Refer to section 15 for specific national regulation.

6.2 Environmental precautions

Environmental precautions : Prevent further leakage or spillage.
Do not flush into surface water or sanitary sewer system.
If the product contaminates rivers and lakes or drains inform respective authorities.

6.3 Methods and material for containment and cleaning up

Methods for cleaning up : Contaminated surfaces will be extremely slippery.
Sweep up or vacuum up spillage and collect in suitable container for disposal.
Clean contaminated surface thoroughly.

6.4 Reference to other sections

For personal protection see section 8., For disposal considerations see section 13.

Version	Revision Date:	SDS Number:	Date of last issue: -
1.0	08.11.2018	330000000017	Date of first issue: 16.11.2016

SECTION 7: Handling and storage

7.1 Precautions for safe handling

- Advice on safe handling : Avoid formation of aerosol.
Provide sufficient air exchange and/or exhaust in work rooms.
Vapours are heavier than air and may spread along floors.
- Advice on protection against fire and explosion : Substance/product is flammable. Vapour/air-mixtures are explosive at intense warming. Fire fighting equipment must be available. Keep away from heat. Keep away from sources of ignition - No smoking. Take measures to prevent the build up of electrostatic charge. Provide appropriate exhaust ventilation at machinery.
- Hygiene measures : General industrial hygiene practice. Handle in accordance with good industrial hygiene and safety practice. Wash hands before breaks and at the end of workday. Avoid contact with skin, eyes and clothing. Avoid breathing vapours, mist or gas. When using do not eat, drink or smoke. Store personal protection equipment in a clean location away from the work area. Keep away from food, drink and animal feedingstuffs.

7.2 Conditions for safe storage, including any incompatibilities

- Requirements for storage areas and containers : Keep container tightly closed in a dry and well-ventilated place.
- Advice on common storage : Keep away from food, drink and animal feedingstuffs.
- Other data : Protect from frost, heat and sunlight. No decomposition if stored and applied as directed.

7.3 Specific end use(s)

- Specific use(s) : see chapter 1
-

SECTION 8: Exposure controls/personal protection

8.1 Control parameters

Contains no substances with occupational exposure limit values.

8.2 Exposure controls

Personal protective equipment

- Eye protection : Safety glasses with side-shields
- Hand protection
- Material : Chloroprene
 - Break through time : > 480 min
 - Glove thickness : >= 0,6 mm
-

Version	Revision Date:	SDS Number:	Date of last issue: -
1.0	08.11.2018	330000000017	Date of first issue: 16.11.2016

Material : Nitrile rubber
 Break through time : > 480 min
 Glove thickness : >= 0,11 mm

Material : Natural Rubber
 Break through time : > 480 min
 Glove thickness : >= 0,5 mm

Material : butyl-rubber
 Break through time : > 480 min
 Glove thickness : >= 0,5 mm

Material : Viton (R)
 Break through time : > 480 min
 Glove thickness : >= 0,7 mm

Remarks : The choice of an appropriate glove does not only depend on its material but also on other quality features and is different from one producer to the other. The suitability for a specific workplace should be discussed with the producers of the protective gloves. The data about break through time/strength of material are standard values! The exact break through time/strength of material has to be obtained from the producer of the protective glove.

Skin and body protection : Impervious clothing
 Choose body protection according to the amount and concentration of the dangerous substance at the work place.

Respiratory protection : No personal respiratory protective equipment normally required.
 In the case of dust or aerosol formation use respirator with an approved filter.

Filter type : Combined particulates and organic vapour type (A-P)
 P2 filter
 or
 P3 filter

Protective measures : Handle in accordance with good industrial hygiene and safety practice.

SECTION 9: Physical and chemical properties

9.1 Information on basic physical and chemical properties

Appearance : paste

Colour : white, grey

Version	Revision Date:	SDS Number:	Date of last issue: -
1.0	08.11.2018	330000000017	Date of first issue: 16.11.2016

Odour	:	faint
Odour Threshold	:	No data available
pH	:	4 - 7
Melting point/range	:	Concentration: 100 g/l (20 °C) > 30 - < 60 °C
Boiling point/boiling range	:	No data available
Flash point	:	> 200 °C
Upper explosion limit	:	No data available
Lower explosion limit	:	No data available
Vapour pressure	:	< 0,1 hPa (20 °C)
Relative vapour density	:	No data available
Density	:	1,2 g/cm ³
Solubility(ies)	:	
Water solubility	:	completely miscible
Partition coefficient: n-octanol/water	:	No data available
Auto-ignition temperature	:	>= 320 °C
Decomposition temperature	:	ca. 360 °C
Viscosity	:	
Viscosity, dynamic	:	No data available
Viscosity, kinematic	:	No data available
Explosive properties	:	Not explosive See section 10.

9.2 Other information

No data available

SECTION 10: Stability and reactivity

10.1 Reactivity

Stable under recommended storage conditions.

10.2 Chemical stability

No decomposition if stored and applied as directed.

Version	Revision Date:	SDS Number:	Date of last issue: -
1.0	08.11.2018	330000000017	Date of first issue: 16.11.2016

10.3 Possibility of hazardous reactions

Hazardous reactions : Vapour/air-mixtures are explosive at intense warming.

10.4 Conditions to avoid

Conditions to avoid : Heat, flames and sparks.
To avoid thermal decomposition, do not overheat.

10.5 Incompatible materials

Materials to avoid : Strong oxidizing agents

10.6 Hazardous decomposition products

Heating or fire can release toxic gas., Carbon monoxide, Carbon dioxide (CO₂)

SECTION 11: Toxicological information

11.1 Information on toxicological effects

Acute toxicity

Product:

Acute oral toxicity Acute : Remarks: No data available

inhalation toxicity Acute : Remarks: No data available

dermal toxicity : Remarks: No data available

Skin corrosion/irritation

Product:

Remarks: No data available

Serious eye damage/eye irritation

Product:

Remarks: No data available

Respiratory or skin sensitisation

Product:

Remarks: No data available

Germ cell mutagenicity

Product:

Genotoxicity in vitro : Remarks: No data available

Version	Revision Date:	SDS Number:	Date of last issue: -
1.0	08.11.2018	330000000017	Date of first issue: 16.11.2016

Genotoxicity in vivo : Remarks: No data available

Carcinogenicity

Product:

Remarks: This information is not available.

Reproductive toxicity

Product:

Effects on fertility : Remarks: No data available

Effects on foetal development : Remarks: No data available

STOT - single exposure

Product:

Remarks: No data available

STOT - repeated exposure

Product:

Remarks: No data available

Repeated dose toxicity

Product:

Remarks: No data available

Aspiration toxicity

Product:

Not applicable

SECTION 12: Ecological information

12.1 Toxicity

No data available

12.2 Persistence and degradability

Product:

Biodegradability : Remarks: Partially biodegradable.

Version	Revision Date:	SDS Number:	Date of last issue: -
1.0	08.11.2018	330000000017	Date of first issue: 16.11.2016

12.3 Bioaccumulative potential

No data available

12.4 Mobility in soil

No data available

12.5 Results of PBT and vPvB assessment

Product:

Assessment : This substance/mixture contains no components considered to be either persistent, bioaccumulative and toxic (PBT), or very persistent and very bioaccumulative (vPvB) at levels of 0.1% or higher..

12.6 Other adverse effects

No data available

SECTION 13: Disposal considerations

13.1 Waste treatment methods

Product : Do not dispose of with domestic refuse.
Offer surplus and non-recyclable solutions to a licensed disposal company.

According to the European Waste Catalogue, Waste Codes are not product specific, but application specific. Waste codes should be assigned by the user, preferably in discussion with the waste disposal authorities.

Contaminated packaging : Empty remaining contents.
Empty containers should be taken to an approved waste handling site for recycling or disposal.

SECTION 14: Transport information

14.1 UN number

Not regulated as a dangerous good

14.2 UN proper shipping name

Not regulated as a dangerous good

14.3 Transport hazard class(es)

Not regulated as a dangerous good

14.4 Packing group

Not regulated as a dangerous good

14.5 Environmental hazards

Not regulated as a dangerous good

14.6 Special precautions for user

Not applicable

Version	Revision Date:	SDS Number:	Date of last issue: -
1.0	08.11.2018	330000000017	Date of first issue: 16.11.2016

14.7 Transport in bulk according to Annex II of Marpol and the IBC Code

Not applicable for product as supplied.

SECTION 15: Regulatory information

15.1 Safety, health and environmental regulations/legislation specific for the substance or mix-ture

Regulation (EC) No 649/2012 of the European Parliament and the Council concerning the export and import of dangerous chemicals : Not applicable

REACH - Candidate List of Substances of Very High Concern for Authorisation (Article 59) : Not applicable

Regulation (EC) No 1005/2009 on substances that deplete the ozone layer : Not applicable

Regulation (EC) No 850/2004 on persistent organic pollutants : Not applicable

Seveso II - Directive 2003/105/EC amending Council Directive 96/82/EC on the control of major-accident hazards involving dangerous substances
Not applicable

Seveso III: Directive 2012/18/EU of the European Parliament and of the Council on the control of major-accident hazards involving dangerous substances.
Not applicable

Volatile organic compounds : Directive 2010/75/EU of 24 November 2010 on industrial emissions (integrated pollution prevention and control)
Volatile organic compounds (VOC) content: 90 %, 1.080 g/l
Remarks: VOC content excluding water

The components of this product are reported in the following inventories:

DSL	:	All components of this product are on the Canadian DSL
AICS	:	Not in compliance with the inventory
NZIoC	:	Not in compliance with the inventory
ENCS	:	Not in compliance with the inventory
ISHL	:	Not in compliance with the inventory
KECI	:	On the inventory, or in compliance with the inventory
PICCS	:	Not in compliance with the inventory
IECSC	:	On the inventory, or in compliance with the inventory

Version	Revision Date:	SDS Number:	Date of last issue: -
1.0	08.11.2018	330000000017	Date of first issue: 16.11.2016

15.2 Chemical safety assessment

A Chemical Safety Assessment is not required for this substance.

SECTION 16: Other information

Full text of other abbreviations

ADN - European Agreement concerning the International Carriage of Dangerous Goods by Inland Waterways; ADR - European Agreement concerning the International Carriage of Dangerous Goods by Road; AICS - Australian Inventory of Chemical Substances; ASTM - American Society for the Testing of Materials; bw - Body weight; CLP - Classification Labelling Packaging Regulation; Regulation (EC) No 1272/2008; CMR - Carcinogen, Mutagen or Reproductive Toxicant; DIN - Standard of the German Institute for Standardisation; DSL - Domestic Substances List (Canada); ECHA - European Chemicals Agency; EC-Number - European Community number; ECx - Concentration associated with x% response; ELx - Loading rate associated with x% response; EmS - Emergency Schedule; ENCS - Existing and New Chemical Substances (Japan); ErCx - Concentration associated with x% growth rate response; GHS - Globally Harmonized System; GLP - Good Laboratory Practice; IARC - International Agency for Research on Cancer; IATA - International Air Transport Association; IBC - International Code for the Construction and Equipment of Ships carrying Dangerous Chemicals in Bulk; IC50 - Half maximal inhibitory concentration; ICAO - International Civil Aviation Organization; IECSC - Inventory of Existing Chemical Substances in China; IMDG - International Maritime Dangerous Goods; IMO - International Maritime Organization; ISHL - Industrial Safety and Health Law (Japan); ISO - International Organization for Standardization; KECI - Korea Existing Chemicals Inventory; LC50 - Lethal Concentration to 50 % of a test population; LD50 - Lethal Dose to 50% of a test population (Median Lethal Dose); MARPOL - International Convention for the Prevention of Pollution from Ships; n.o.s. - Not Otherwise Specified; NO(A)EC - No Observed (Adverse) Effect Concentration; NO(A)EL - No Observed (Adverse) Effect Level; NOELR - No Observable Effect Loading Rate; NZIoC - New Zealand Inventory of Chemicals; OECD - Organization for Economic Cooperation and Development; OPPTS - Office of Chemical Safety and Pollution Prevention; PBT - Persistent, Bioaccumulative and Toxic substance; PICCS - Philippines Inventory of Chemicals and Chemical Substances; (Q)SAR - (Quantitative) Structure Activity Relationship; REACH - Regulation (EC) No 1907/2006 of the European Parliament and of the Council concerning the Registration, Evaluation, Authorisation and Restriction of Chemicals; RID - Regulations concerning the International Carriage of Dangerous Goods by Rail; SADT - Self-Accelerating Decomposition Temperature; SDS - Safety Data Sheet; TCSI - Taiwan Chemical Substance Inventory; TRGS - Technical Rule for Hazardous Substances; TSCA - Toxic Substances Control Act (United States); UN - United Nations; vPvB - Very Persistent and Very Bioaccumulative

Further information

Sources of key data used to compile the Safety Data Sheet : The specifications are based on information by upstream suppliers., The sources indicated below only refer to information on the individual ingredients and not to the mixture., Safety data sheets by various manufacturers., ECHA Classification and Labelling - echa.europa.eu/de/view-article/-/journal_content/07005f81-abf1-4081-973b-6c7c526c39df, ECHA Information on Registered Substances. <http://apps.echa.europa.eu/registered/registered-sub.aspx>, UMWELTBUNDESAMT [www.umweltbundesamt.de/wgs/wgs-index.htm]

Information Data Sheet

diamond paste type GARANT



Version	Revision Date:	SDS Number:	Date of last issue: -
1.0	08.11.2018	330000000017	Date of first issue: 16.11.2016

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text.

GB / EN