



## Husqvarna K 7000

The Husqvarna K 7000 is the new version of Husqvarna's 16-inch PRIME™ power cutter. A machine that is continuously gathering new fans attracted by the high power and easy handling, useful in many applications both indoors and outdoors. Delivering a 6 in (155 mm) cutting depth, this model is very useful for pre-cutting before deepcutting with the new Husqvarna K 7000 Ring or K 7000 Chain power cutters. The Husqvarna K 7000 comes with a number of new features including the updated, maintenance-free 8 hp (6 kW) permanent magnet highfrequency motor with smooth blade stop function.



### Impressive power

High power output which operates on both 3-phase (5.5 kW) at 180-480 V and 1-phase (1.5-3 kW) 120-240 V.



### Increased comfort and safety

Comfortable stop time on the rotating blade giving increased comfort and safety when paired with PP 70.

### Higher productivity

Increased cutting performance giving higher productivity when paired with PP 70.



### Magnesium blade guard

Contributes to a light weight which gives an improved power-to-weight ratio and cutting depth now up to 155 mm. New stepless adjustment makes it easier to change cutting position.



## PXM\_FEATURES

- Higher productivity
- Increased comfort and safety
- Impressive power
- Magnesium blade guard for improved power-to-weight ratio
- Reliable and efficient
- The ergonomic design with low system weight and well balanced body with optimally positioned handles minimize the strain on your body.
- Automatically optimised power and rpm
- Overload protection by LED indicator
- A powerful electric cutter for both indoor and outdoor use
- Wet cutting is supported by easily adjustable water flow during operation. The water flow starts first when the trigger lock-out is activated.
- The blade on all of our electric cutters rotates forward, cutting into the material efficiently, minimizing the risk of sticking and kickbacks.

Technical Specifications	
<b>CAPACITY</b>	
Output power	7.4 hp
Output power, 1 phase	4.0 hp
Output power, 3 phase	7.4 hp
Output shaft RPM, max	4300 rpm
Peripheral speed, max	18000 fpm
Rated input power	4/ 7.4 hp
Water flow, min	0.1 gal (US)/min
Water pressure, max	116 psi
<b>DIMENSIONS</b>	
Article gross weight	13200 g
Article net weight	9800 g
Arbor diameter	1 in
Blade diameter, max	16 in
Blade flange diameter	5 in
Blade thickness, max	0.2 in
Cutting depth, max	6 in
Product size height	19 in
Product size length	26.8 in
Product size width	7.4 in
Weight	21.6 lbs
<b>ENGINE</b>	
Electronic product	Yes
Engine cooling	Water
<b>EQUIPMENT</b>	
Rated current	10/16 A
Water connector	Gardena Male
<b>LUBRICANTS</b>	
Engine cooling	Water
<b>SOUND AND NOISE</b>	
Sound power level, guaranteed (LWA)	111 dB(A)
Sound power level, measured	104 dB(A)
Sound pressure level at operators ear	93 dB(A)
<b>VIBRATIONS</b>	
Daily Vibration (Aeqv)	1.8 m/s <sup>2</sup>
Daily Vibration Exposure (A8)	0.64 m/s <sup>2</sup>
Daily Vibration Time (Time factor)	1 h
Vibrations left/front handle	1.8 m/s <sup>2</sup>
Vibrations right/rear handle	1.8 m/s <sup>2</sup>
<b>PACKAGING</b>	
Packaging length	710 mm
Packaging width	230 mm
Packaging height	485 mm
Packaging volume	79.2 dm <sup>3</sup>