# **ESD Vinyl Mats and Mat Kits**

## **3059 Series**

#### **RoHS & REACH Compliant**

Three Layer ESD Mats are ideal for static dissipative and flexible work surfaces. They are made of a textured vinyl with a buried conductive layer in between provides a superior physical and electrical qualities. A homogenous construction, our three-layer mat consists of solid polyvinyl chloride surrounding a layer of conductive fleece, giving it consistent electrical properties in addition to superior physical properties.

#### **Applications**

- **Electronic Assembly and Manufacturing**
- Pharmaceutical Plants and Cleanroom Operation
- Fiber Optics, Aerospace, and Hospitals


### **Product Specifications** (1)

COLOR	Blue, Dark Gray	
EMBOSS PATTERN	Kid Grain	
GAUGE /THICKNESS	0.094" ± 0.010"; 3 /32"	
TENSILE	900 lbs./in.² minimum	ASTM D412, Die C
ELONGATION	125%	ASTM D412, Die C
TEAR	150 lbs./in.	ASTM D624, Die C
DUROMETER	85 ± 5, Shore A	ASTM D2240
ESD Properties: Range @ 10 V	$3.0 \times 10^7 - 9.5 \times 10^8$ ohms/sq.	ESD S4.1-1997
Suggested Service Temperature	–20 °F to +160 °F <sup>(2)</sup>	

- (1) Specifications are subject to change at any time. If you have any questions, please contact us for the latest update.
- (2) This suggested range represents the general temperature range for most flexible vinyl products

Bertech® makes no warranty, representation, or guarantee regarding the information contained herein or the suitability of its this product for any particular purpose, nor does Bertech® assume any liability whatsoever arising out of the application or use of this product. It is ultimately the responsibility of the customer to determine a product's suitability for a particular application.







#### Bertech

640 Maple Ave Torrance, CA 90503 Phone: (310) 787-0337

Email: sales@bertech.com

www.bertech.com

# PRODUCT DATA SHEET