



# Pan Head - Type I (Phillips)



This type of recess has a large center opening, tapered wings, and blunt bottom, with all edges relieved or rounded.



## GRADE MARK

THREAD DATA		
Size: #6	Threads per in.: 32	Series Designation: UNC
Thread Class or Type: 2A	Major Diameter: 0.1372 - 0.1312	Pitch and Functional Dia.: 0.1169 - 0.1141
Tensile Stress Area: 0.0091	Standard: ASME B1.1 - 2003 (R2008)	Length: 2
Length Tolerance: -0.06		
DIMENSIONAL DATA		
Type: Pan Head - Type I (Phillips)	Standard: ASME B18.6.3 - 2013	Nominal Diameter: 0.138
A - Head Diameter: 0.270 - 0.256	H - Head Height: 0.097 - 0.087	Driver Size: 2
Penetration Depth: 0.080 - 0.055	Wobble: 12°	M - Ref. Recess Dim.: 0.159
PHYSICAL REQUIREMENTS		
Nominal: 0.138	Standard: ASME B18.6.3-2013, Machine Screw (Stainless Steel)	Typical Materials: 304 Stainless Steel
Hardness: HRB 90 ref.	Tensile Load, Min. (lbf): 545	Yield PSI, 2% Offset, Machined Specimen: 40,000
Tensile Strength, Min. (psi): 80,000	Calculated Shear Load-BODY (ref.)(lbf): 327	Calculated Shear Load-THREADS (ref.)(lbf): 273
Straightness Factor: 0.012	Calculated Pretension <sup>2</sup> (lbf) : 273	Tightening Torque <sup>1</sup> : 1 ft.lbf, 7 in.lbf, 0.8 Nm
FINISH DATA		
Finish: As received steel (RoHS Compliant)	K factor (ref. DIN 946): 0.18	

<sup>1</sup> These torque values are based on K factors determined using DIN 946, tightening tension of 75% of the yield strength, and the calculation formula  $T=KDP$ . These values are advisory only. The torque for assembling critical joints should be determined and/or verified through actual experimentation by the user. The IFI is not responsible for any losses or claims resulting from the use of these values. <sup>2</sup> Calculated Pretension is equal to 75% of the bolt's yield strength achieved when using the indicated Tightening Torque.