



## Product Specification

### Product:

G01 cartridge

### Description:

G01 OV cartridge for use with 9000 series facepiece

Sizes: Small – 9100

Medium – 9200

Large – 9300

Full facepiece – 9900

### Performance Specification:

per NIOSH 42 CFR part 84A

OV – organic vapor

Can be used with P95 Particulate Filter model G95P:

Sodium Chloride @ 85 lpm maximum penetration 5%

DOP (dioctyl phthalate) Oil @ 85 lpm maximum penetration – non degrading 5%

### Airflow Resistance:

Initial Inhalation: 40 mm water column height pressure @ 85 lpm

Initial Inhalation with P95 filter: 50 mm water column height pressure @ 85 lpm

Initial Exhalation: 20 mm water column height pressure @ 85 lpm

Leakage 30 milliliters per minute @ 25 mm water column height

### Materials:

Cartridge body:

ABS

Carbon filled

### Approvals:

NIOSH

G01 with half mask approval TC-23C-1526

G01 with full facepiece approval TC-23C-2722

G01 with G95P with half mask approval TC -84A-3332

G01 with G95P with full facepiece approval TC -84A-5509

January 8, 2013

RAB