



Solid carbide roughing end mill HPC, TiXSi, Ø f8 DC: 16mm



Order data

Order number	203044 16
GTIN	4045197679413
Item class	12X

Description

Version:

For **roughing and finishing**.

Up to 1.5×D into solid material **at very high feed rates** with smooth cutting action.

Advantage:

Optimised flute form, eccentric relief ground, wide chip space.

Technical description

Cutting edge Ø D _c	16 mm
Feed f _z for side milling in steel < 900 N/mm ²	0.1 mm
Corner chamfer width at 45°	0.3 mm
Overhang length L ₁ incl. recess	42 mm
Recess Ø D ₁	15.5 mm
No. of teeth Z	4
Feed f _z for slot milling in steel < 900 N/mm ²	0.08 mm
Shank Ø D _s	16 mm
Overall length L	92 mm
Flute length L _c	36 mm
Direction of infeed	horizontal, oblique and vertical
Shank	DIN 6535 HB to h6
Tolerance nominal Ø	f8

Helix angle	38 degrees
Corner chamfer angle	45 degrees
Coating	TiXSi
Tool material	Solid carbide
Standard	DIN 6527
Type	N
Helix angle characteristic	unequal spacing
Spacing of the cutters	unequal spacing
Cutting width a_e for milling operation	0.3×D for side milling
Cutting width a_e for milling operation	Full slot cutting depth 1×D
Through-coolant	no
Machining strategy	HPC
Colour ring	green
Type of product	End / face mill

User data

	Suitability	V_c	ISO code
Steel < 500 N/mm ²	suitable	250 m/min	P
Steel < 750 N/mm ²	suitable	200 m/min	P
Steel < 900 N/mm ²	suitable	180 m/min	P
Steel < 1100 N/mm ²	suitable	160 m/min	P
INOX < 900 N/mm ²	suitable only under restricted conditions	70 m/min	M
GG(G)	suitable only under restricted conditions	120 m/min	K
Uni	suitable		
wet maximum	suitable		
wet minimum	suitable only under restricted conditions		
dry	suitable		

Air

suitable