




PRINT MAY BE REDUCED - DO NOT SCALE.



Sydney (Head Office) Ph: 1300 795 953  
 15 Waltham St Fax: (02) 9439 9815  
 Artarmon, 2064 www.makinex.com.au  
 NSW, Australia sales@makinex.com.au

COPYRIGHT 2015 MAKINEX.  
 WARNING: Copyright in this drawing remains the property of MAKINEX and copying in whole or part is not permitted without the written authority of the copyright owner.

GENERAL TOLERANCES  
 (Unless otherwise noted)  
 0-100mm: ± 0.25 mm  
 100mm - 500mm: ± 0.5 mm  
 500mm +: ± 1.0 mm  
 Angular: ± 1 deg.



DATE: 9/02/2021

SCALE: D.N.S A3

All Dimensions are in Millimetres  
 Break All Sharp Corners and  
 Remove Burrs & Swarf



PROJECT:

DWG NO.

JHT-U-2

NOTES:

TITLE

JACKHAMMER TROLLEY -  
 UNIVERSAL V2

MATERIAL

SEE PARTS

FINISH

SEE PARTS

DRN: JT

MASS

REV

004

SHEET 1 OF 5

PRINTED: 9/02/2021

ITEM NO.	PART NO.	PART NAME	QTY
1	JHT-03-00	MAIN FRAME WELDMENT	1
2	JHT-02-01	RESTING BLOCK	1
3	JHT-02-02	SPRING BRACKET	1
4	JHT-99-21	M12 SPRING PLUNGER	1
5	JHT-99-12	CE PLATE	1
6	MAK-UP-529	M3X10 BLIND RIVET (ALUMINIUM)	2
7	MAK-UP-530	M8X35 CSK BOLT Z/P	2
8	MAK-UP-511	M8 NYLOC NUT	2
9	MAK-UP-531	M12x1.5 HEX HALF NUT	1
10	MAK-UP-53	GREASE NIPPLE	1
11	JHT-05-00	BASE FRAME WELDMENT	1
12	JHT-04-01	PIVOT AXLE	1
13	JHT-04-02	BOLT HOLDER	2
14	JHT-04-21	CABLE PROTECTOR	1
15	JHT-99-42	COTTER SPLIT PIN	1
16	MAK-UP-08	NYLON WASHER 16MM	2
17	MAK-UP-06	NYLON WASHER 20MM	4
18	MAK-UP-532	M8X20 CSK BOLT Z/P	2
19	MAK-UP-533	M8X25 CSK BOLT Z/P	2
20	MAK-UP-534	M8X25 HEX BOLT Z/P	2
21	MAK-UP-535	M8 FLAT WASHER (MEDIUM)	6
22	MAK-UP-511	M8 NYLOC NUT	4
23	MAK-UP-516	M8 SPRING WASHER	2
24	JHT-07-00	HANDLE FRAME WELDMENT	1
25	JHT-06-01	HANDLE BUFFER	1
26	JHT-06-02	HANDLE NUTBAR	1
27	JHT-06-03	CABLE CLIP	1
28	MAK-UP-10	RUBBER HANDLE GRIPS WITH CABLE HOLDER	2
29	MAK-UP-175	HANDLE END PLUG	2
30	JHT-99-63	BRAKE LEVER & CABLE SET	1
31	MAK-UP-536	M12X50 HEX BOLT Z/P	2
32	MAK-UP-537	M12 FLAT WASHER (MEDIUM)	2
33	MAK-UP-538	M12 SPRING WASHER	2
34	MAK-UP-539	M4X12 CSK PH BOLT Z/P	2


ITEM NO.	PART NO.	PART NAME	QTY
35	JHT-99-17	10MM DIA ANCHOR SHACKLE-1T	1
36	JHT-08-02	LOWERING PIN	1
37	JHT-08-03	SMALL SPRING	1
38	JHT-99-81	R-CLIP	1
39	MAK-UP-507	M6 HEX NUT	1
40	MAK-UP-517	M8 HEX NUT	2
41	MAK-UP-516	M8 SPRING WASHER	1
42	MAK-UP-540	M16 FLAT WASHER (MEDIUM)	1
43	JHT-01-01	TENSION SPRING	1
44	MAK-UP-00	MAKINEX WHEEL 250MM	2
45	MAK-UP-03	WHEEL BUSH 20MM	4
46	JHTB-U-2	JHT BLOCKSET-UNIVERSAL V2	1



Sydney (Head Office) Ph: 1300 795 953  
 15 Waltham St Fax: (02) 9439 9815  
 Artarmon, 2064 www.makinex.com.au  
 NSW, Australia sales@makinex.com.au

COPYRIGHT 2015 MAKINEX.  
 WARNING: Copyright in this drawing remains the property of MAKINEX and copying in whole or part is not permitted without the written authority of the copyright owner.

GENERAL TOLERANCES  
 (Unless otherwise noted)  
 0-100mm: ± 0.25 mm  
 100mm - 500mm: ± 0.5 mm  
 500mm +: ± 1.0 mm  
 Angular: ± 1 deg.



DATE: 9/02/2021

SCALE: D.N.S A3

All Dimensions are in Millimetres  
 Break All Sharp Corners and  
 Remove Burrs & Swarf



PROJECT:

DWG NO. TITLE MATERIAL FINISH

JHT-U-2 JACK HAMMER TROLLEY - UNIVERSAL V2 SEE PARTS SEE PARTS

NOTES:


DRN: JT

MASS REV

004

SHEET 2 OF 5

PRINT MAY BE REDUCED - DO NOT SCALE.




ITEM NO.	PART NO.	PART NAME	QTY
1	JHT-09-02	CUTOUT TOP PLATE	1
2	JHT-09-11-1	B-BLOCK V2	2
3	JHT-09-14	B2 ADAPTOR	2
4	JHT-09-12	F BLOCK	2
5	JHT-09-15	F1 ADAPTOR	2
6	MAK-UP-541	M10X250 HEX BOLT	4
7	MAK-UP-542	M10 FLAT WASHER (MEDIUM)	6
8	MAK-UP-543	M10 NYLOC NUT	6
9	JHT-09-21	B3 ADAPTOR	2
10	JHT-09-13	B1-ADAPTOR (BLUE VER)	2
11	MAK-UP-613	M10X270 HEX BOLT	2
12	JHT-09-06	HILTI F BLOCK TOP PLATE	1
13	MAK-UP-545	M10X65 HEX BOLT	2
14	MAK-UP-511	M8 NYLOC NUT	2
15	MAK-UP-544	M8X65 HEX BOLT	2
16	MAK-UP-160	P CLIP 10mm	1
17	JHT-09-19	HILTI TOP HANDLE PIECES, NEW	1



Sydney (Head Office) Ph: 1300 795 953  
 15 Waltham St Fax: (02) 9439 9815  
 Artarmon, 2064 www.makinex.com.au  
 NSW, Australia sales@makinex.com.au

COPYRIGHT 2015 MAKINEX.  
 WARNING: Copyright in this drawing remains the property of MAKINEX and copying in whole or part is not permitted without the written authority of the copyright owner.

GENERAL TOLERANCES  
 (Unless otherwise noted)  
 0-100mm: ± 0.25 mm  
 100mm - 500mm: ± 0.5 mm  
 500mm +: ± 1.0 mm  
 Angular: ± 1 deg.



DATE: 9/02/2021

SCALE: D.N.S A3

All Dimensions are in Millimetres  
 Break All Sharp Corners and  
 Remove Burrs & Swarf



PROJECT:

DWG NO.

JHTB-U-2

NOTES: EXPLODED VIEW

TITLE

UNIVERSAL BLOCK SET V2

MATERIAL

SEE PARTS

FINISH

SEE PARTS

DRN: MCAPE

MASS REV

3061.852 G 001

SHEET 4 OF 5

PRINTED: 9/02/2021