

PIG® Overpack Salvage Drum

PAK384 Storage Capacity 65 gal.,UN1H2/X200/S,Thickness .25"

Tough enough for rough handling, guaranteed. Ship your hazardous materials in our UN Rated, FDA-Compliant overpacks to stay compliant with regs.

- Tough UN Rated overpack is built to withstand rough handling. Guaranteed.
- X-rated for Packing Groups I, II and III, so it's ideal for regulated packaging applications, including shipping hazardous materials by land, sea or rail
- Polyethylene material with UV inhibitors is durable, lightweight and chemical-resistant
- Containers are nestable when empty to save storage space
- Designed and proven to withstand the abuse of shipping to help keep hazardous materials safely contained
- Specifically designed and sized for leaking drums up to 30 gallons
- Leakproof, twist-on lid is notched so you can easily tighten it with a 2x4 or pole
- Integrated ledges molded into container let you move overpack with a forklift
- Made from FDA-Compliant resins for containment of food and cosmetic products



Specifications

Dimensions	ext. dia. 27.75" x 37.5" H
Storage Capacity	65 gal.
Brand	PIG
Bung Type	No Bung Holes
Drum Type	Poly Drum
Interior Dimensions	22" Dia. x 34.25" H
Color	White
Lid Type	Open-Head - Screw-Top
Lining	Unlined
Thickness	.25"
Sold as	1 each
Weight	49 lbs.
# per Pallet	3
Composition	Polyethylene

UNSPSC

24112109

Pigalog® Page Number

Page 299

Metric Equivalent

Storage Capacity

246 L

Weight

22.2 kg

Dimensions

ext. dia. 70cm x 95cm H

Technical Information

Certifications, Approvals and Ratings

Meets FDA requirements, UN1H2/X200/S

Technical Documents

LDPE Products

Instructions for Overpack Containers

49 CFR 173.3(c)(1)



New Pig

World's best stuff for leaks, drips and spills.

One Pork Avenue • Tipton, PA 16684-0304

1-855-493-4647 • Fax: 1-800-621-7447 • newpig.com • hothogs@newpig.com