

PIG® Poly Spill Containment Cart

PAK648 For 5 to 55 gal. Drums, Load Capacity 500 lbs., Sump Capacity 57 gal.

Provides up to 57 gallons of mobile hazardous waste containment with primary and secondary sumps that are easy to empty and clean.

- Sump holds up to 57 gallons
- Grate and drain plug remove easily for emptying and cleaning of sumps
- Helps you meet 40 CFR 264.175 for containment of hazardous waste (depending on containers stored)
- Lockable wheels prevent accidental rolling to add safety



Specifications

Sump Capacity Range	40 - 69.9 gal.
Use With	5 to 55 gal. Drums
Dimensions	29" W x 66.5" L x 16" H
Load Capacity UDL	500 lbs.
Sump Capacity	57 gal.
Brand	PIG
Color	Black/White
Caster/Wheel Included	Included
Caster/Wheel Quantity	4
Caster/Wheel Type	(2) 8" Polyolefin Casters & (2) 10" Polyolefin Wheels
Drum Type	Steel Drum; Poly Drum; Fiber Drum; Overpack; Steel Bucket; Poly Bucket
Drum Size	5 gal.; 8 gal.; 10 gal.; 16 gal.; 20 gal.; 30 gal.; 55 gal.
Special Feature	Lockable Wheels

Use With Flammables	No
Sold as	1 each
Weight	119 lbs.
# per Pallet	5
Composition	Sump: Polyethylene Grate: Structural Foam Handle: Steel Wheels: Polyolefin
UNSPSC	24101905
Pigalog® Page Number	<u>Page 326</u>

Metric Equivalent

Sump Capacity	215.7 L
Load Capacity UDL	226.8 kg
Weight	54 kg
Dimensions	74cm W x 169cm L x 41cm H

Technical Information

Technical Documents

LDPE Products

40 CFR 112.7

40 CFR 122.26

40 CFR 264.175



One Pork Avenue • Tipton, PA 16684-0304

1-855-493-4647 • Fax: 1-800-621-7447 • newpig.com • hothogs@newpig.com