

## **PIG® Overpack Salvage Drum**

PAK708 Storage Capacity 20 gal., UN1H2/X46/S, Thickness .125"



Tough enough for rough handling, guaranteed. Ship your hazardous materials in our UN Rated, FDA-Compliant overpacks to stay compliant with regs.

- Tough UN Rated overpack is built to withstand rough handling. Guaranteed.
- X-rated for Packing Groups I, II and III, so it's ideal for regulated packaging applications, including shipping hazardous materials by land, sea or rail
- Polypropylene material with UV inhibitors is durable, lightweight and chemical-resistant
- Containers are nestable when empty to save storage space
- Designed and proven to withstand the abuse of shipping to help keep hazardous materials safely contained
- Specifically designed and sized for leaking cans, bottles or 5-gallon pails
- Two broom holes 180-degrees opposite each other on the lid allow 100% positive leverage for easy opening and closing with a broom handle or bar
- Integrated ledges and handles molded into container let you move overpack with a forklift or by hand; foot hold in the drum base allows you to hold the drum securely in position while opening or closing the lid
- Apply a tamperproof seal to alignment holes on lid and drum to ensure contents aren't disturbed
- Features enhanced lid and base design for added strength and security for stacking or if the drum is accidentally dropped
- Made from FDA-Compliant resins for containment of food and cosmetic products

Item#	Description	Dimensions	Weight
PAK708-WH		ext. dia. 23" x 19" H	13 lbs.

### Metric Equivalent:

Item#	Description	Dimensions	Weight
PAK708-WH		ext. dia. 58cm x 48cm H	5.9 kg

### Specifications

<b>Dimensions</b>	ext. dia. 23" x 19" H
<b>Storage Capacity</b>	20 gal.
<b>Brand</b>	PIG
<b>Bung Type</b>	No Bung Holes
<b>Drum Type</b>	Poly Drum
<b>Interior Dimensions</b>	16.75" Dia. x 16.5" H
<b>Lid Type</b>	Open-Head - Screw-Top
<b>Lining</b>	Unlined
<b>Thickness</b>	.125"
<b>Sold as</b>	1 each
<b>Weight</b>	13 lbs.
<b>New Pig Patent</b>	10,273,038
<b># per Pallet</b>	12
<b>Composition</b>	Injection Molded Copolymer Polypropylene
<b>UNSPSC</b>	24112109
<b>Pigalog® Page Number</b>	<a href="#">Page 299</a>

## Metric Equivalent

<b>Storage Capacity</b>	75.7 L
<b>Weight</b>	5.9 kg
<b>Dimensions</b>	ext. dia. 58cm x 48cm H

## Technical Information

### Certifications, Approvals and Ratings

Meets FDA requirements, UN1H2/X46/S

### Technical Documents

[Instructions for Overpack Containers](#)

49 CFR 173.3(c)(1)



**One Pork Avenue • Tipton, PA 16684-0304**

1-855-493-4647 • Fax: 1-800-621-7447 • [newpig.com](http://newpig.com) • [hothogs@newpig.com](mailto:hothogs@newpig.com)